


500 Series



Color Quality Control from Start to Finish

The 500 Series of spectrodensitometers capture density, color and spectral data. Available with a variety of aperture size options and configurable for left- or right-handed use, the 500 Series feature full menu commands, offering consistent color measurements between different presses, suppliers, and customers.



The 500 Series family includes:

504 Basic model measures density quickly and reliably.

508 Prepress and pressroom densitometer for accurately measuring density, dot area, and dot gain.

518 Densitometer for 4-color press operators utilizing measurement functions such as density, dot gain, dot area, trap, and print contrast.

528 For printers who print special and process colors. Offering a full selection of densitometric capability, plus several essential color measurement features.

530 Advanced spectrodensitometer for pressroom, ink lab or testing lab providing spectral, color, and density measurements. Connects to X-Rite's IntelliTrax auto scanning system, and complements X-Rite's ColorMaster, InkFormulation and other software applications.

Rugged Design

X-Rite revolutionized densitometry with the first portable instruments, and the 500 Series is the industry standard for ruggedness. The targeting window pinpoints the measurement area, so you get the right measurement every time. You can select from our three standard measuring areas, or use the microspot measuring area for smaller color targets.

Pick-and-Measure Menu

Depending on your model and its features, you can select density, dot, color, and other densitometry particulars right from the menu and start measuring. It's that easy to get accurate results. You can also let the instrument auto-pick the right function using Electronic Function Select. It will select density, dot, or trap automatically based on the color target you measure.

Feature Selection

Select only the features you want to see on the main screen, and change them back again later. This can be helpful when instruments are used in multiple areas, or to make operation of the 500 easier for new users. Managers can even lock a set of selected features to prevent tampering.

Easy Upgrades

Upgrade your existing 500 Series model to a higher model number as your needs change, maintaining the value of your investment. The upgrade process simply requires a custom keycode. You can also add helpful accessories like polarization and UV exclusion or a battery charging station.

Unrivaled Warranty

All 500 Series instruments come with our industry-leading three-year warranty. You can be sure of solid, reliable and accurate performance beyond the warranty period with our long-term service agreements and ISO certification services.

Dependable Results

X-Rite's technology produces the highest level of inter-instrument agreement available today. This means you can trust your 500 Series to give you comparable color measurements between two or more presses or printing sites, among suppliers, or between the customer and the printing facility.



One-Step Calibration

Each 500 Series instrument comes with a form-fitting white reference, so calibration takes only a few seconds. Use the built-in reminder to prompt you when to calibrate, ensuring consistent, accurate measurements each and every time.

Easy-to-Read Graphic Display

The 500 Series has an easy-to-read graphic display. It's configurable for left- or right-handed operation and features full menu commands in multiple languages* to meet the needs of almost any user, anywhere.

* Chinese, English, French, German, Italian, Japanese, Portuguese, Spanish and more



500 Series Product Feature Comparison:

| | | 504 | 508 | 518 | 528 | 530 | |
|-------------------------|---|---|-----|-----|-----|------|------|
| Density Measurement | Density (absolute or minus paper) | | | | | | |
| | Density References (16) | • | • | • | • | • | |
| | News Density Mode | | | | | | |
| | News Gray Balance Mode | • | • | • | • | • | |
| | Apparent Dot Area (Tone Value) | | | | | | |
| | Dot Gain (Tone Value Increase) | | • | • | • | • | |
| | Apparent Trap | | | | | | |
| Apparent Trap Reference | | | | • | • | • | |
| Color Measurement | Print Contrast | | | | | | |
| | Print Contrast Reference | | | • | • | • | |
| | Hue Error / Grayness, Hue Error / Grayness Reference | | | • | • | • | |
| | Electronic Function Select (EFS) | | | • | • | • | |
| | CIE L*a*b* | | | | • | • | |
| | CIE L*C*h° (ab), L*C*h° (uv) | | | | • | • | |
| | Hunter Lab | | | | • | • | |
| | XYZ | | | | • | • | |
| | ΔE* CIELAB, ΔE CMC, ΔE*94 | | | | • | • | |
| | Yxy, L*u'v', Yu'v' | | | | • | • | |
| | Colorimetric Graphing | | | | • | • | |
| | Match | | | | • | • | |
| | Compare | | | | • | • | |
| | Spectral Reflectance | Spectral Data Output, Spectral Graphing | | | | | • |
| | | Paper | | | | • | • |
| | Database | Color References | | | | 1424 | 1424 |
| | | PANTONE® FORMULA GUIDE (coated, uncoated, matte) | | | | • | • |
| Warranty | 3 year warranty | • | • | • | • | • | |
| Software | ColorMail Express | | | | • | • | |

Specifications:

| | | |
|------------------------|----------------------------|--|
| Measurement conditions | Illuminant types | A, C, D50, D55, D65, D75, F2, F7, F11, F12 |
| | Standard observers | 2°, 10° |
| | Response types | ISO Status T, ISO Status E, ISO Status I, ISO Status A, G, Tx, Ax, Ex, Hi-Fi |
| Measurement technology | Spectral range | 400nm to 700nm |
| | Measurement geometry | 45°/0° per ANSI, DIN & ISO Standards |
| | Measurement aperture | 3.4mm (.13in) standard 2.0mm (.078in) optional 6.0mm (.236in) optional Micro-Spot: 1.6mm (.063in, H) x 3.2mm (.125in, W) optional |
| | Light source | Gas Pressure @ 2856° |
| | Physical filters | No (incandescent lamp light), Optional Polarized, Optional UV cutoff |
| | Measurement time | Approx. 1.4 seconds per single measurement Approx. 0.9 seconds in Speed Read mode |
| | Measurement range | 0.00D–2.5D; 0–160%R |
| | Inter-instrument agreement | ±0.01 D or 1% for typical printing processes 0.40 ΔE CMC MAX on 12 BCRA Tiles |
| | Density repeatability | ±0.005D for 0.00–2.00D* ±0.010D for 2.00–2.50D* *Polarized Yellow: ±0.010D for 0.00–1.80D Micro-Spot: ±0.010D for 0.0–1.8D |
| | Data interface | Serial data interface |
| Power supply | Power source | Ni-MH battery pack, 4.8v rated @ 1650mAh |
| | Charge time | Approximately 3 hours |
| Environmental | Operating temperature | +10°–35°C |
| | Humidity | 30%–85%RH non condensing |
| Mechanical data | Physical dimensions | Length: 197mm (7.8in) Width: 76mm (3.0in) Height: 81mm (3.2in) |
| | Weight | 1050 grams (2.3lbs.) |